


● PRODUCT INTRODUCTION ●



|                      |                                      |          |
|----------------------|--------------------------------------|----------|
| □□□□□□               | □□□                                  |          |
| □□□□□                | □□□□□ □□□□□□□ □□□□□ □□□□□            |          |
| □□□□ PP.             | PP                                   |          |
| □□□□□□               | 50 □□□□□□ □□□□□□□□ □□□□ □□□          |          |
| Gaslift.             | 85 □□□□□□□ □□□□□□□□□□MM              |          |
| □□□□□                | 2.0MM □□□□□□ □□□□□ □□ □□□□□□ □□□□□□□ |          |
| □□□□□                | 35 □□□□□□□ □□□□□□□□□□kgs (5 □□)      |          |
| □□□□□□□□ □□□□□       | 12 □□□□□□□□ □□□□□ □□□□ □□□           |          |
| □□□□□                | PP □□ ArderFibre Armrest             |          |
| □□□□□ □□□            | *                                    |          |
| □□□□□□               | 310mm pp □□ flassfibre □□□□□□        |          |
| headrest.            | Y.□□□□□                              |          |
| □□□□□ □□□□□          | *                                    |          |
| □□ / □□□             | □ □□□□□□□itth.                       |          |
|                      | □ □□□□□□□epth.                       |          |
|                      | □□□□□□□□□□ □□□□□                     |          |
|                      | □ □□□□□□□itth.                       |          |
|                      | □ □□□□□□□epth.                       |          |
|                      | □□□□□□□□□□ □□□□□                     |          |
|                      | □ □□□□□□□itth.                       |          |
| □□□□□                | 2.□□□□□□□□□□ □□□□□□ / CTN.           |          |
| CBM.                 | 0.082./□□□□□□□□□                     |          |
| □□□□ / □□□□□□□ □□□□□ | 20GP.                                | 40 □□□□□ |
|                      | 360-410.                             | 870-920. |

● PARTS REFERENCE ●



WORKSHOP



● ENGINEERING CASE ●



OUR PHOTOS



---

CERTIFICATE

---

SGS

Test Report No. 201904080171 Date: Apr 10, 2019 Page 1 of 1

Weight: 14.20kg

Sample Description: 170 mm x 110 mm x 1.2 mm (3) 2019-04-08-0171

Other Description: Chair frame 400 mm x 1100 mm x 1200 mm

**Sample Photos**

**Test Results**

SGS

Test Report No. 201904080171 Date: Apr 10, 2019 Page 1 of 1

Weight: 14.20kg

Sample Description: 170 mm x 110 mm x 1.2 mm (3) 2019-04-08-0171

Other Description: Chair frame 400 mm

**Sample Photos**

**Test Results**

SGS

Test Report No. 201904080171 Date: Apr 10, 2019 Page 1 of 1

Weight: 14.20kg

Sample Description: 170 mm x 110 mm x 1.2 mm (3) 2019-04-08-0171

Other Description: Chair frame 400 mm

**Sample Photos**

**Test Results**

SGS

Test Report No. 201904080171 Date: Apr 10, 2019 Page 1 of 1

Weight: 14.20kg

Sample Description: 170 mm x 110 mm x 1.2 mm (3) 2019-04-08-0171

Other Description: Chair frame 400 mm x 1100 mm x 1200 mm

**Sample Photos**

**Test Results**

SGS

Test Report No. 201904080171 Date: Apr 10, 2019 Page 1 of 1

Weight: 14.20kg

Sample Description: 170 mm x 110 mm x 1.2 mm (3) 2019-04-08-0171

Other Description: Chair frame 400 mm

**Sample Photos**

**Test Results**

SGS

Test Report No. 201904080171 Date: Apr 10, 2019 Page 1 of 1

Weight: 14.20kg

Sample Description: 170 mm x 110 mm x 1.2 mm (3) 2019-04-08-0171

Other Description: Chair frame 400 mm

**Sample Photos**

**Test Results**

SGS

Test Report No. 201904080171 Date: Apr 10, 2019 Page 1 of 1

Weight: 14.20kg

Sample Description: 170 mm x 110 mm x 1.2 mm (3) 2019-04-08-0171

Other Description: Chair frame 400 mm

**Sample Photos**

**Test Results**

SGS

Test Report No. 201904080171 Date: Apr 10, 2019 Page 1 of 1

Weight: 14.20kg

Sample Description: 170 mm x 110 mm x 1.2 mm (3) 2019-04-08-0171

Other Description: Chair frame 400 mm

**Sample Photos**

**Test Results**

# SHIPPING

15-25 40 \* 1 15-35 40 \* 2

EX Works CIF C & F LC

100

100

# OUR SERVICE

100

100

100

D. 000000 0000 00 0000000000.

E. 000000000 000000 00000000.

00000000) 000000 0000 0000).

00000000 0000000 0000000000 0000000 00000000 0000000 00 000000 0000 :0000000 0000 00 000000 000000

000000 00 00000000 0000000000 0000000 00000000 0000000000 0000000000 0000000000 00000000 000000

00000000 00 00000000000 000000000 0000000000.

## FAQ

**q1:** 00000000 0000 000000000 000000000 00

a: sure.sample 15-7 00 0000000 000000 00 000000 .0000000 0000 000000days 0000000 000000000 0000.

**q2:** 00000 00000000 00 000000000 00

a: 0000000 0000000 00000000000 000000 0000000.

**q3:** 0000000000000 000000 00000000 00000000 00

0000000 5 00000000 000000 00 .000000000 000000 0000 0000 0000 000000 000000 0000 0000 :0.

**q4:** 0000000000 000000 00 0000000000 000000000 0000 00

a: 00000000 0000000 00 0000000 10 00 0000000 0000000000 0000000000 00000000 0000.

**q5:** 00000000 000000 00 000000

a: 00000000 000000 0000 T / T (0000000000 0000 0000000000 0000 0000000000 0000 0000000000)

000000 00 000000000 000000000000 0000000000 0000000000 000000000000.

## CONTACT US



Manager : Rachel

**Whatsapp/Wechat:**

0086-13590681820



**E-mail:**

rachel@new-city.cn